

## Improved listening in a variety of situations...

### ► Busy, noisy environments

Conversor Pro allows you to focus on the desired sound source. Its directional microphone greatly reduces unwanted sounds coming from the sides and the rear.

### ► Quieter sounds

Conversor Pro automatically amplifies desired sounds, allowing you to hear clearly, even quieter sounds, without straining or having to turn up your hearing instrument.

### ► Relaxed conversations


Conversor Pro provides greatly enhanced sound level and clarity, allowing you to interact with family, friends or work colleagues in a more relaxed manner.

### ► Watching television

Conversor Pro and TV Pro enable you to enhance your viewing experience.

### ► Group settings


Conversor Pro Multipack provides a system solution for multiple hearing aid wearers for schools, colleges and groups.




In a classroom or lecture hall



In a busy restaurant or café



Watching television



Travelling in a car

## Enhanced sound quality wherever you are...



## For further information contact

### Conversor Limited

The Lansbury Estate,  
102 Lower Guildford Road  
Knaphill, Woking, Surrey  
GU21 2EP (UK)

Telephone: +44 (0) 870 066 3499

Freephone: 0800 298 9982 (UK only)

Fax: +44 (0) 870 066 3669

Email: [info@conversorproducts.com](mailto:info@conversorproducts.com)

Web: [www.conversorproducts.com](http://www.conversorproducts.com)

Pro Fam v1.0 © Conversor Limited

# conversor Pro

The Clarity of Sound

## Assistive Listening Devices



[www.conversorproducts.com](http://www.conversorproducts.com)

## Anywhere for active lifestyles

Introducing the **Conversor® Pro** range of affordable **assistive listening devices (ALDs)** - offering the versatility needed to enjoy everyday life.

Offering comfort, ease of use and wireless portability, Conversor Pro ALDs are the perfect companion for anyone with a hearing difficulty. All products are designed for easy use with Telecoil equipped hearing instruments, cochlear implants, headphones or earbuds.

Conversor Pro ALDs enable easy listening and relaxed conversation in the classroom or office, at social gatherings, travelling in the car, when out shopping, at home or just watching the TV or listening to the radio.

## Designed for comfortable and discreet use

**Conversor Pro** focuses on a desired sound source and by filtering out background noise, the desired sound is much clearer and more intelligible. Even in noisy environments, by increasing the available sound level, less strain is placed on the hearing instrument amplifiers, eliminating distortion and feedback.

Conversor Pro consists of two lightweight components - a transmitter / microphone and a pendant receiver.



A **Conversor Pro** user can focus on the sounds they want to hear by selecting either the zoom setting, for focused hearing and one-to-one conversations or the omni-directional setting for group discussions and social gatherings.

The transmitter/microphone can be;

- held in the hand and pointed directly at the desired sound source
- worn by a speaker moving about the house; in lecture and classroom situations
- placed in close proximity to the sound source while the user wearing the pendant receiver is up to 50 metres (150 feet) indoors or up to 100 metres (300 feet) outdoors
- connected directly to a TV, radio, VCR/DVD/CD player or computer for enhanced hearing enjoyment.

The pendant receiver is worn around the user's neck and sends the much improved sound received from the transmitter wirelessly to either a hearing instrument, cochlear implant or binaural headphones or earbuds, which are easily plugged into the receiver.



A local microphone on the pendant receiver enables the user to operate it as an independent assistive listening device for amplification of one-to-one conversations.

The Conversor Pro transmitter/microphone can broadcast to as many pendant receivers as required, making it ideal for group situations. Both the transmitter/microphone and pendant receiver are quickly rechargeable for up to ten hours of continuous use.



▲ **Conversor TV Pro** enhances sound from a TV, radio, VCR/DVD/CD player or computer.

The TV Pro transmitter plugs directly into the sound source and transmits to the Conversor Pro pendant receiver.



▲ **Conversor Pro Plus** includes the Conversor Pro and TV Pro transmitters and a Conversor Pro pendant receiver giving ultimate flexibility for your listening requirements in any situation.



### ▲ **Conversor Pro Multipack**

This is the ideal solution for groups with varying hearing needs. Multipack is used in schools, universities, conference facilities and by tour guides world-wide.

Multipack is a robust charging case which can hold up to 12 separate transmitters and/or receivers. Transmitters and receivers can be programmed to different frequencies by Conversor, the distributor or a trained operator.

## Conversor Pro can help you hear in a wide variety of situations

Conversor Pro ALDs provide optimal sound quality and versatility through a unique set of features:

### ▶ **Background noise reduction**

The Conversor Pro reduces unwanted background and peripheral sound by up to 30db.

### ▶ **Wireless transmission**

Lets the transmitter/microphone be placed near the sound source, transmitting back to the user with clarity, up to 100 metres (300 feet) away.

### ▶ **Zoom setting**

Allows the user to focus on one particular sound while background or peripheral sounds are greatly reduced.

### ▶ **Omni-directional setting**

Picks up nearby sounds clearly from all around the user, ideal for family dinners or meetings.